

Workman[®] Tripod Features & Benefits

	FEATURES	BENEFITS
EASY TO USE	Simple setup	Saves time and promotes correct use
	Maximum height line on tripod legs	The max. height line allows for quick and easy set up to maximum tripod height without the need to count holes or guess where to insert the pins.
	Legs automatically lock in the open position	Easy set up and added safety
	No need for a separate pulley/bracket assembly	Fewer attachment pieces enable faster set up
	Telescoping legs (up to 8 ft. high)	Allow for compact storage and height adjustment for a wide variety of applications
	Anodized aluminum legs and aluminum head	Reduces weight for greater portability
	Accessories can attach to any leg	Simplifies setup and improves ease of use
	Entry/retrieval equipment attached on outside of tripod legs	Provides optimal clearances inside/under the tripod to prevent interference with workers entering/exiting confined space
DURABLE	Internal leg-locking mechanism (head)	Prevents leg collapse in the event the tripod is moved during use
	Cut-resistant pin retention chains	Increased service life and improved durability
	Skid-resistant feet with integral leg base support strap	Improved stability and strength of entire system
VERSATILE	Leg base support strap converts to convenient carrying strap	Provides an easy way to carry the tripod to and from jobs
	Legs feature 4in. incremental adjustments that improve tripod stability when used on uneven surfaces	Easy setup and independent leg adjustment to meet special application needs
	Unit is "backwards compatible" with the Lynx Hoist and Lynx Rescuer	Eliminates the need to upgrade/ purchase new accessories



Note: This bulletin contains only a general description of the products shown. While uses and performance capabilities are described, under no circumstances shall the products be used by untrained or unqualified individuals and not until the product instructions including any warnings or cautions provided have been thoroughly read and understood. Only they contain the complete and detailed information concerning proper use and care of these products.



ID 2301-93-MC / Dec 2009
© MSA 2009 Printed in U.S.A.

Corporate Headquarters
P.O. Box 426, Pittsburgh, PA 15230 USA
Phone 412-967-3000
www.MSAnet.com

U.S. Customer Service Center
Phone 1-800-MSA-2222
Fax 1-800-967-0398

MSA Canada
Phone 1-800-672-2222
Fax 1-800-967-0398

MSA Mexico
Phone 01 800 672 7222
Fax 52-44 2227 3943

MSA International
Phone 412-967-3354
FAX 412-967-3451

Offices and representatives worldwide
For further information:

